


Model 5054 Triaxial Cable Assembly Triaxial 2 Lug Male Each End, On Belden 9222 Triaxial Cable



MATERIALS:

Connector – 1st End: Triaxial Cable Male (BNC 2 Lug Bayonet Style)

Body and Fittings: Brass, Tarnish Resistant

Intermediate and Center contacts: Gold Plated Brass per MIL-C-39012

Cable: Belden 9222 Triaxial Cable

20 AWG stranding 7x28, T.C. Polyethylene Insulation, 6.15 (.242) O.D. Color: Yellow

Marking: “POMONA ELECTRONICS 5054-XX”

Connector – 2nd End: Same as first.

RATINGS:

Operating Voltage: 500 VRMS

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 5054-XX

XX = Length in inches. Std. Lengths: 36”, 60”

Additional lengths can be quoted upon request.

Ordering Example: 5054-36, Cable length will be 36” long

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5054-60](#) [5054-36](#) [EM5054-240](#)