

**AMP** AMP Connect

MAIN MENU HELP  
FAMILIES REGISTRATION

Alphabetical Picture Part Number  
**SEARCH SEARCH SEARCH**

Go To Step Search™ Screen


**350780-1** -- 1 of 1 products

Soft Shell Connectors

Soft Shell - Housings, Test Connectors and IDC Connectors

General **INFO**  
Sales **INFO**  
Customer Drawings **SPECIFICATIONS**

2, 3, 4, 5, 6, 8 and 10  
Circuit, In-Line



Line art represents typical product only.

 [Panel Cutout](#)

<b><i>Searchable Features:</i></b>	
<b>Product Type</b>	Housing
<b>Connector Line</b>	Universal MATE-N-LOK
<b>Contact Diameter</b>	.084 [2.13] in. [mm]
<b>Centerline</b>	.250 [6.35] in. [mm]
<b># of Circuits</b>	4
<b>Contact Layout</b>	In-Line
<b>Mating Type</b>	Cap
<b>Mount</b>	Free or Panel
<b>Packaging Method</b>	One Piece Housing
<b>Housing Material</b>	Nylon
<b>Color</b>	White
<b>Lock Type</b>	Positive Lock
<b><i>Other Properties:</i></b>	
<b>Dim. A (Panel Cutout)</b>	1.065 [27.05] in. [mm]
<b>Dim. B (Panel Cutout)</b>	.340 [8.64] in. [mm]
<b>Dim. C (Panel Cutout)</b>	.095 [2.41] in. [mm]
<b>Dim. D (Panel Cutout)</b>	.530 [13.46] in. [mm]
<b>Dim. E (Panel Cutout)</b>	.250 [6.35] in. [mm]
<b>Dim. X</b>	1.051 [26.70] in. [mm]
<b>Housing Flammability Rating</b>	UL 94V-0
<b>Packaging Quantity</b>	100