

RJ45 10G RJ45 plug Cat6, 8p IDC straight



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 151 1560
Specification	RJ45 10G RJ45 plug Cat6, 8p IDC straight
HARTING eCatalogue	https://b2b.harting.com/09451511560

Identification

Category	Connectors
Series	HARTING RJ Industrial®
Element	Cable connector
Specification	Straight

Version

Termination method	IDC termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8

Technical characteristics

Conductor cross-section	0.1 ... 0.32 mm ² solid and stranded
Conductor cross-section	AWG 27 ... AWG 22 solid and stranded
Wire outer diameter	≤1.6 mm
Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP20
Cable diameter	4.5 ... 9 mm
Transmission characteristics	Cat. 6 Class E _A up to 500 MHz



Pushing Performance

Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate

Specifications and approvals

Specifications	IEC 60603-7 Mating face
	IEC 11801
	EN 50173-1
	EN 45545-2 R26: HL1, HL2, HL3
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	24.74 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440101 Rectangular connectors (set)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09451511560](#)