

Coaxial Cable Connector 11_MMBX-50-2-1/111_N

Description

Straight cable plug

Interface standards
SUHNER-MMBX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	12.4 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0007 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Related Documents

Outline drawing	DOU-00006163
Catalogue drawing	DOU-00006165
Assembly instruction	DOC-0000179377

Ordering Information

Single package	11_MMBX-50-2-1/111_NE
----------------	-----------------------

Additional Information

Suitable cables	RG_316_/U, RG_188_A/U, RG_174_/U
-----------------	----------------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11_MMBX-50-2-1/111_NE](#)