

## Coaxial Cable Connector 11\_N-50-9-9/033\_-

### Description

Straight cable plug

QUICK-FIT connector  
 For outdoor applications  
 Water protection according to IP 68



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz
Frequency range	DC to 3 GHz
Return loss	≥ 30 dB
Intermodulation	≤ Static -155 dBc (2 x 43 dBm carrier)

#### Mechanical Data

Centre contact	plugged
Outer contact	clamped
Weight	0.1117 kg

#### Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	NR (Natural Rubber)	

### Related Documents

Outline drawing	DOU-00006926
Catalogue drawing	DOU-00006928
Assembly instruction	DOC-0000179418

### Ordering Information

Single package	11_N-50-9-9/033_-E
----------------	--------------------

### Additional Information

Suitable cables	SUCOFEED_1/2_HF, SUCOFEED_1/2_HF_FR, SUCOFEED_1/2_HF_FR_UL, Heliax FSJ4-50B, NK Cables RFF 1/2-50, Cellflex SCF12-50
Interface standards	IEC 61169-16_MIL-STD-348A/304_CECC 22210

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11\\_N-50-9-9/033\\_-E](#)