

Coaxial Cable Connector 11_SMA-50-3-100/111_N

Description

Straight cable plug

Interface standards
SUHNER-SMA-26.5GHz



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 26.5 GHz

Mechanical Data

Centre contact soldered
Outer contact soldered
Weight 0.0028 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Coupling nut	Bronze	Gold Plating (Nickel underplated)
Gasket	VMQ (Silicone rubber)	

Related Documents

Catalogue drawing DCA-00007238
Assembly instruction DOC-0000181590

Ordering Information

Bulk 100 pcs package 11_SMA-50-3-100/111_NH
Single package 11_SMA-50-3-100/111_NE

Additional Information

Suitable cables EZ_141_TP_M17, SUCOFORM_141, MULTIFLEX_141

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11_SMA-50-3-100/111_NE](#)