


Coaxial Cable Connector 11_SMA-50-3-16/-11_N

Description

Straight cable plug

Interface standards
SUHNER-SMA-26.5GHz



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 26.5 GHz

Mechanical Data

Outer contact soldered
Weight 0.0019 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact		
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Coupling nut	Bronze	Gold Plating (Nickel underplated)
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing DOU-00007822
Catalogue drawing DOU-00006518
Assembly instruction DOC-0000179294

Ordering Information

Bulk 100 pcs package 11_SMA-50-3-16/-11_NH

Additional Information

Suitable cables EZ_141_TP_M17

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11_SMA-50-3-16/-11_NH](#)