

# HUBER+SUHNER® DATA SHEET

## Coaxial Cable Connector: 16\_MMCX-50-1-4/111\_O



### Description

Right angle cable plug

Interface Standards  
SUHNER-MMCX



### Technical Data

#### Electrical Data

Impedance 50 Ω  
Interface frequency max. 6 GHz

#### Mechanical Data

Centre contact soldered  
Outer contact soldered  
Weight 0.0007 kg

#### Environmental Data

Operating Temperature -55 °C to 155 °C  
2002/95/EC (RoHS) compliant

#### Material Data

##### Piece Parts

Centre contact	Copper Beryllium Alloy
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE

##### Surface Plating

Gold Plating (Nickel underplated)  
Gold Plating (without Nickel underplating)  
Gold Plating (without Nickel underplating)

#### Related Documents

Catalogue drawing	DOU-00006007
Assembly instruction	DOC-0000179220

#### Ordering Information

Single package	16_MMCX-50-1-4/111_OE
Bulk 100 pcs package	16_MMCX-50-1-4/111_OH

#### Additional Information

Suitable cables	EZ_47_TP_M17, SUCOFORM_47_CU
-----------------	------------------------------

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
RF Technology  
9100 Herisau, Switzerland  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
www.hubersuhner.com

**HUBER+SUHNER – Excellence in Connectivity Solutions**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[16\\_MMCX-50-1-4/111\\_OH](#)