


## Coaxial Cable Connector 25\_N-50-3-4/133\_N

### Description

Straight panel cable jack, flange mount

Interface standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	11 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0426 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

### Related Documents

Catalogue drawing	DCA-00008794
Assembly instruction	DOC-0000177464
Mounting hole	DOU-00008795

### Ordering Information

Single package	25_N-50-3-4/133_NE
----------------	--------------------

### Additional Information

Suitable cables	RG_223_/U, RG_142_B/U, RG_400_/U
-----------------	----------------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[25\\_N-50-3-4/133\\_NE](#)