

## Within Series Adaptor 32\_MBX-50-0-3/111\_N

### Description

Adaptor plug/plug  
MBX plug (male) / MBX plug (male)

Slide - snap interface

Interface standard  
Series MBX - HUBER+SUHNER MBX



### Technical Data

#### Electrical Data

Impedance 50 Ω  
Interface frequency max. 6 GHz

#### Mechanical Data

Number of matings 100  
Weight 0.001754 kg

#### Environmental Data

Operating temperature -55 °C to 155 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Interface - MBX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Body	Bronze	Gold Plating
Insulator	PFA / PTFE / LCP	

Interface - MBX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Body	Bronze	Gold Plating
Insulator	PFA / PTFE / LCP	

### Related Documents

Outline drawing DOU-00145652

### Ordering Information

Bulk 100 pcs package 32\_MBX-50-0-3/111\_NH  
Single package 32\_MBX-50-0-3/111\_NE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[32\\_MBX-50-0-3/111\\_NE](#)