

Coaxial PCB Connector 82_MMBX-50-0-14/111_N

Description

Straight PCB jack

Interface Standards
SUHNER-MMBX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 12.4 GHz

Mechanical Data

Board mounting type through holes
Weight 0.0007 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------------------------|-----------------|
| Centre contact | Brass | SUCOPRO Plating |
| Outer contact | Brass | SUCOPRO Plating |
| Body | Brass | SUCOPRO Plating |
| Insulator | LCP (Liquid crystal polymer) | |

Related Documents

Outline drawing DOU-00002008
Mounting hole DOU-00002008

Ordering Information

Bulk 100 pcs package 82_MMBX-50-0-14/111_NH
Single package 82_MMBX-50-0-14/111_NE
Tape and Reel package 82_MMBX-50-0-14/111_NM

Remarks

PCB connector with stand-offs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[82_MMBX-50-0-14/111_NE](#)