


## Coaxial PCB Connector 82\_MMCX-S50-0-2/111\_K

### Description

Straight PCB jack

Interface Standards  
SUHNER-MMCX



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 6 GHz

#### Mechanical Data

Board mounting type edge mount  
Weight 0.0007 kg

#### Environmental Data

Operating temperature -55 °C to 155 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

### Related Documents

Outline drawing DOU-00013081  
Catalogue drawing DCA-00013083

### Ordering Information

Bulk 100 pcs package 82\_MMCX-S50-0-2/111\_KH  
Tape and Reel package 82\_MMCX-S50-0-2/111\_KG  
Single package 82\_MMCX-S50-0-2/111\_KE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[82\\_MMCX-S50-0-2/111\\_KG](#)