## **Data Sheet**

# **HUBER+SUHNER**

## **Coaxial PCB Connector** 85\_SMA-50-0-101/111\_N

#### Description

Right angle PCB jack

Interface Standards IEC 60169-15\_MIL-STD-348A/310\_CECC 22110



### **Technical Data**

Electrical Data Impedance Interface frequency max.	50 Ω 18 GHz
<b>Mechanical Data</b> Board mounting type Weight	through holes 0.0039 kg
Environmental Data Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102)	-65 °C to 165 ° compliant

65 °C compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

#### **Related Documents**

Outline drawing Catalogue drawing

DOU-00012830 DCA-00012832

#### **Ordering Information**

Single package Bulk 100 pcs package 85\_SMA-50-0-101/111\_NE 85\_SMA-50-0-101/111\_NH

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER: 85\_SMA-50-0-101/111\_NH