


# solenoid coil

## VACF-B-B2-1A

Part number: 8030804

FESTO

Type B connection pattern, industry standard, 24 V AC/50-60 Hz



### Data sheet

Feature	Value
Assembly position	Any
Duty cycle	100 %
Insulation class	H
Characteristic coil data	24 V AC: 50/60 Hz, pick-up power 3.9 VA, holding power 2.6 VA
Permissible voltage fluctuation	+/- 10 %
Authorisation	c UL us - Recognized (OL)
Maritime classification	see certificate
Certificate issuing department	DNVGL-TAA000011J
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Medium temperature	-20 ... 50 °C
Protection class	IP65
Ambient temperature	-20 ... 50 °C
Electrical connection	To industry standard (11 mm) Plug pattern type B to EN 175301-803
Mounting type	With knurled nut
Materials note	Conforms to RoHS
Material housing	PA Steel
Material solenoid coil	Copper Steel Thermoplastic
Material winding	Copper