





A1RFRD10

REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD



PC Board Thickness=1.60mm  
PC Board Component Side Shown



**NOTES:**

**ELECTRICAL:**

- VOLTAGE RATING : 125 VAC RMS.
- CURRENT RATING : 1.5 AMP.
- CONTACT RESISTANCE : 50 MILLIOHMS MAX.
- INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
- DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.

**MECHANICAL:**

- HOUSING MATERIAL : NYLON+30%.G.F(FR52) UL94V-0.
- INSERT : NYLON+30%.G.F(FR52) UL94V-0.
- CONTACT MATERIAL : PHOSPHOR BRONZE t=0.35mm.
- PLATING : GOLD PLATING OVER NICKEL.
- OPERATING LIFE : 750 CYCLES MIN.
- PCB RETENTION PRE-SOLDER : 1 LB MIN.
- PCB RETENTION POST-SOLDER: 10 LBS MIN.

**ENVIRONMENTAL:**

- STORAGE : -40°C TO +85°C.
- OPERATION: 0°C TO 70°C.
- WAVE SOLDERING TEMPERATURE: 255~265° (5~10 SECONDS)

MATES WITH MODULAR PLUG CONFORMING TO FCC PART 68, SUBPART F.

UL & CUL FILE NO. E163191  
PART NUMBER:E5908-0T03XX-L

- 4- W/ FRE LOGO 1- 3u" 2- 6u"
- U- W/O FRE LOGO 3- 15u" 4- 30u"
- 5- 50u"

DETACHED LISTS	MM (INCH)	DFTO QIANPU	DATE 3/15/05	<b>FULL RISE ELECTRONIC CO., LTD</b>	
	TOLERANCES EXCEPT AS NOTED	CHKDSAMMY	DATE2005/3/15		
	MM	MFO	DATE		
	.0 ± 0.2 ±	APPVILUSHENG	DATE2005/3/15		
.00 ± 0.15 ±	MATERIAL :			TITLE RJ45 STAMPED PIN III STACKED GANG JACK (2x1)	
.000 ± 0.075 ±	ANGLES ± 0.5	QTY :			DRAWING NO. GE593B81-LA
	THIRD ANGLE PROJECTION	FINISH :			/PART NO. SEE NOTES
		SCALE : 2:1			DO NOT SCALE DRAWING
					SHEET 1 OF 1

SIZE REV  
A3 0

8

7

6

5

4

3

2

1

H  
G  
F  
E  
D  
C  
B  
A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[E5908-0T0343-L](#)