

PUZZLE-IN003B

Desktop Network Appliance with Intel® Atom® Processor C3000
 Processor support up to 6 x 1 GbE, 2 x 10 GbE & 2 x M.2 slots, 1 x PCIe Mini, 1 x eMMC 32GB



Features

- Intel® Atom® processor C3558 8M Cache, up to 2.20 GHz
- Support 4 x 1 GbE NIC via Intel® C3558, 2 x 1 GbE PHY via Marvell 88E1512, 2 x 10 GbE SFP+ via intel C3558
- DDR4 2133 MHz ECC (by CPU) or non-ECC UDIMM/R-DIMM Up to 128GB
- 1 x M.2 A key (USB 2.0, PCIe x1), 1 x miniPCIe (USB 2.0, PCIe x1) with SIM card slot, 1 x eMMC 32GB

Specifications

		PUZZLE-IN003B-C0	PUZZLE-IN003B-C1
Platform	Form Factor	Desktop	
	CPU	Intel® Atom® processor C3758 16M cache, up to 2.20 GHz	Intel® Atom® processor C3558 8M cache, up to 2.20 GHz
	Chipset	Integrated in CPU	
Memory	Memory Technology	DDR4 2133 MHz ECC (By CPU) or non-ECC UDIMM, Support DDR4 RDIMM	
	Memory Capacity	UDIMM up to 64GB / RDIMM up to 128GB	
	Memory Socket	4 x 288-pin DIMM	
Network and Security	Network Acceleration and Security Function	<ul style="list-style-type: none"> • Intel® AES New Instructions • Intel® Software Guard Extensions (Intel® SGX) • Intel® Memory Protection Extensions (Intel® MPX) • Intel® Virtualization Technology for Directed I/O (VT-d) • Intel® QuickAssist Technology (Intel® QAT) 	<ul style="list-style-type: none"> • Intel® AES New Instructions • Intel® Software Guard Extensions (Intel® SGX) • Intel® Virtualization Technology for Directed I/O (VT-d) • Intel® QuickAssist Technology (Intel® QAT)
	TPM	1 x TPM 2.0 pin header	
Networking	Ethernet IC	1 GbE NIC: Intel® i211-AT 1 GbE PHY: Marvell 88E1512 10 GbE: Intel® X553 integrated in CPU	
	Ethernet Port	4 x 1GbE from Intel® i211-AT 2 x 1GbE from Marvell 88E1512 2 x 10 GbE SFP+	
	Network Module Slot	N/A	
Expansion Slot	PCIe Slot	N/A	
	PCIe Mini Card Slot	1 x PCIe Mini card (PCIe 3.0, USB 2.0) with SIM slot	
	M.2	1 x M.2 A key (PCIe 3.0& USB 2.0)	
Storage	Storage	1 x SATA 3.0 + 1 x 5V power connector (for SATA DOM) 1 x M.2 M key 2260/2280 Support PCIe 3.0 x4 nVME	
	eMMC	1 x eMMC 32GB	
	SD Card	N/A	
External I/O	USB	1 x USB 2.0 1 x USB 3.2 Gen 1	
	Console	1 x RJ-45	
Internal I/O	HDMI	N/A	
	USB	N/A	
Power and Mechanical	Power Switch	1 x Power switch	
	Reset Button	1 x Reset button	
	Power Input	1 x DC jack	
	Type/Watt	12 V DC-in, 60W	
	Processor Cooling	Passive CPU heatsink	
	System Cooling	Two system fans	Fanless
Physical and Environmental	Antenna Hole	2 x Antenna hole	
	Storage Temperature	-20°C ~ 75°C (-4°F ~ 167°F)	
	Operating Temperature	0°C ~ 40°C (32°F ~ 104°F)	
	Operating Humidity	5% ~ 90% non-condensing	
	Dimensions (W x L x H) (mm)	225 x 206 x 44.2	
Weight	2 kg		
OS and Certifications	Certification	CE / FCC / RoHS	
	Operating System	Linux Ubuntu 18.04.04 CentOS 7 / Red Hat / Fedora EPEL Microsoft Windows 10	
Indicators	LCM	N/A	
	LED	1 x Power LED, 1 x Storage LED, 1 x Alert LED	

Ordering Information

Part No.	Description
PUZZLE-IN003B-C0-R10	Desktop network appliance with Intel® ATOM® C3758 processor, 4 x DDR4 slots, 6 x 1GbE, 2 x 10 GbE & 2 x M.2 slots, 1 x PCIe Mini slot, 1 x eMMC 32GB, RoHS
PUZZLE-IN003B-C0/8G-R10	Desktop network appliance with Intel® ATOM® C3758 processor, one 8GB DDR4, 6 x 1GbE, 2 x 10 GbE & 2 x M.2 slots, 1 x PCIe Mini slot, 1 x eMMC 32GB, RoHS
PUZZLE-IN003B-C1-R10	Desktop network appliance with Intel® ATOM® C3558 processor, 4 x DDR4 slots, 6 x 1GbE, 2 x 10 GbE & 2 x M.2 slots, 1 x PCIe Mini slot, 1 x eMMC 32GB, RoHS
PUZZLE-IN003B-C1/8G-R10	Desktop network appliance with Intel® ATOM® C3558 processor, one 8GB DDR4, 6 x 1GbE, 2 x 10 GbE & 2 x M.2 slots, 1 x PCIe Mini slot, 1 x eMMC 32GB, RoHS


Packing List

	PUZZLE-IN003B-C0-R10	PUZZLE-IN003B-C0/8G-R10	PUZZLE-IN003B-C1-R10	PUZZLE-IN003B-C1/8G-R10
Power cord	1	1	1	1
Power adapter	1	1	1	1
Rack mounting ears	Option	2	Option	2
Screws for rack mounting ears	Option	6	Option	6
USB to console cable	Option	1	Option	1
RS-232 to console cable	1	Option	1	Option


Options

Item	Part No.	Description
USB to console cable	32013-004000-100-RS	Round cable, LAN cable, FTDI console cable, 2, 1800MM, (A) USB A TYPE 4P MALE+PCB:FTDI_FT232RL, (B) RJ-45 8P8C, RoHS
RS-232 to console cable	32005-005100-100-RS	Round cable, RS-232/422/485, PUZZLE RS-232 cable, 2, 500MM, 24AWG, (A) D-SUB 9P MALE+#4-40 screw, (B) RJ-45 PLUG 8P8C, ONE PCS PKG, TC&C, RoHS
Rack ear mounting kit	19B00-000417-00-RS	Accessory module: PUZZLE-IN003 series rack ear mounting kit


IO Interface



Rear view



Dimensions (Unit: mm)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IEI:](#)

[PUZZLE-IN003B-C0/8G-R10](#) [PUZZLE-IN003B-C1/8G-R10](#) [PUZZLE-IN003B-C0-R10](#) [PUZZLE-IN003B-C1-R10](#)