



PC Board Layout Component Side Shown

REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD

NOTES:

ELECTRICAL:

- VOLTAGE RATING : 125 VAC RMS.
- CURRENT RATING : 1.5 AMP.
- CONTACT RESISTANCE : 45 MILLIOHMS MAX.
- INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
- DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:

- HOUSING MATERIAL : PBT+30%G.F UL94V-0.
- INSETER MATERIAL : PBT+30%G.F UL94V-0.
- CONTACT MATERIAL : PHOSPHOR BRONZE t=0.35mm.
- PLATING : GOLD PLATING OVER NICKEL.
- OPERATING LIFE : 750 CYCLES MIN.
- PCB RETENTION PRE-SOLDER : 1 LB MIN.
- PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:

- STORAGE : -40°C TO +85°C.
 - OPERATION: 0°C TO 70°C.
 - WAVE SOLDER TEMPERATURE: 230°C TO 250°C 5~10 SECONDS.
- MATES WITH MODULAR PLUG CONFORMING TO
FCC PART 68, SUBPART F.
CUL FILE NO. E163191
ROHS PART NUMBER: E5688-XSC08X-L

- 1- 3U" 2- 6U"
 - 3- 15U" 4- 30U"
 - 5- 50U"
- SHIELD
2 w/o logo TIN
3 w/o logo NICKEL

DETACHED LISTS	MM (INCH)	DFTO ANKUE	DATE 11/25/05
	TOLERANCES EXCEPT AS NOTED	CHKDASHLELLY	DATE 2005/11/25
	MM	MFO	DATE
	.0 ±0.20	APPVLLUSHENG	DATE 2005/11/25
	.000 ±0.075	MATERIAL :	
ANGLES ±	QT'Y :		
THIRD ANGLE PROJECTION	FINISH :		
	SCALE :		

FULL RISE ELECTRONIC CO., LTD

TITLE
11.5 SIDE ENTRY PCB JACK 8P (W/TABS)

DRAWING NO. GE563135-LC
/PART NO. SEE NOTE

SIZE A3
REV 0

DO NOT SCALE DRAWING SHEET X OF Y

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[E5688-3SC084-L](#)