

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0194340003**
Status: **Active**
Overview: MX150L Industrial Sealed Connector System
Description: MX150L Female Terminal for 10-12 AWG Wire

Documents:

Drawing (PDF)	Brochure (PDF)
Product Specification PS-19432-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-19434-001 (PDF)	

Agency Certification

CSA	LR18689
UL	E152602

General

Product Family	Crimp Terminals
Series	<u>19434</u>
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	UL E152602
Crimp Quality Equipment	Yes
Overview	<u>MX150L Industrial Sealed Connector System</u>
Packaging Alternative	<u>194340001 (Reel)</u>
Product Name	MX150L
UPC	822350193153


Physical

Gender	Female
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	0.844/g
Packaging Type	Bag
Wire Insulation Diameter	3.94mm-4.45mm
Wire Size AWG	10, 12
Wire Size mm ²	N/A

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-19434-001
Product Specification	PS-19432-001-001
Sales Drawing	SD-19434-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19434 Series

Mates With

19431 Male Terminal

Use With

19432 Female Receptacle

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Toolkit for	<u>2002220700</u>
MX150 Connectors	
Hand Crimp Tool for	<u>638115300</u>
Crimp Terminals	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION