



REV	ECRN	DATE
1	NEW PRODUCTION	20190403



NO	CUSTOMER'S ITEM	LENGTH	TOLERANCE	SUPPLIER'S ITEM
1		152MM	±5MM	9.00ACCA2484.00AR
2		305MM	±10MM	9.00ACCA2484.00BR


PIN WIRING



NOTES:

1. ELECTRICAL TEST: 100% OPEN, SHORT & MIS WIRE TEST.
2. CONTACT RESISTANCE: 10 ohm,
3. INSULATOR RESISTANCE: 5M ohm.
4. HIGH VOLTAGE: DC 300V 0.01sec.
5. MUST BE ROHS COMPLIANT.

⑧					
⑦					
⑥					
⑤		TIE	WHITE TIE L=70mm	5	PCS
④	J.000008.0500R	TIN WIRE	TIN WIRE OD:0.8MM	5	G
③		MOLDING	PVC 45P Red, white, green, black, yellow	10	G
②		TERMINAL	Banana head Ø 3.0 mm phosphor copper nickel plated	10	PCS
①	A.000X07.0302R	CABLE	UL 2733 16AWG*1C PVC 60P jacket: Red, white, green, black, yellow OD=3.0±0.15mm L=LENGTH	5	PCS
NO.	PART NO	ITEM	DESCRIPTION	Q'TY	UNIT

RoHS COMPLIANT			 朋联电子有限公司 DongGuan PengLian Electronics Co.,Ltd TEL: 076938835098/38835095 FAX: 076938835091		
DRAWN BY		袁小政	20190403	比例: FREE	TITLE: Banana terminal wire
CHECKED BY				单位: mm	SUPPLIER'S ITEM: 9.00ACCA2484.00XR
APPROVED BY					CUSTOMER:
					CUSTOMER'S ITEM:
				DRAWING NO. ACCA-2484	DATE 2019.04.03

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[CAB-15368](#)