

USB to Null Modem Serial FTDI Adapter Cable with COM Retention (USB-A to DB9 M/F), 18-in. (45.72 cm)

MODEL NUMBER: **U209-18N-NULL**



Connect a RS-232 Null Modem serial device to the USB-A port on your computer, laptop or tablet.

Features

Converts USB Port into RS-232 Null Modem Serial Port

- Solves DCE/DTE conflicts without additional cross-wired serial cables or adapters
- Supports data transfer speeds up to 256 Kbps—twice as fast as a built-in serial port
- No external power source required
- Portable 18 in. design fits perfectly into laptop bag
- COM retention for automatic reassigning of COM values to ports in case of disconnection or reboot
- Integrated FTDI FT232RL chipset

First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Molded nickel-plated connectors with gold-plated contacts for optimal signal quality
- Integral strain relief for long life
- Flexible PVC jacket easy to install in tight spaces

Broad Compatibility

- Compatible with Windows, Mac and Linux operating systems

Specifications

OVERVIEW

Highlights

- Supports data transfer speeds up to 256 Kbps
- Premium foil and braid shielding reduces EMI/RFI line noise
- Compatible with Windows®, Mac® and Linux®
- No external power source required
- Integrated FTDI FT232RL chipset

System Requirements

- Computer or other device with available USB port and Windows XP or later, Mac OS X 10.3 or later, or Linux

Package Includes

- U209-18N-NULL USB to Null Modem Serial FTDI Adapter Cable (USB-A to DB9 M/F), 18 in.
- Driver CD
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332198297
Technology	Serial (RS232); USB
INPUT	
Bus Powered	Yes
PHYSICAL	
Color	Black; Silver
Cable Jacket Rating	VW-1
Cable Length (ft.)	1.5
Cable Length (m)	0.5
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	3.81 x 9.40 x 11.43
Shipping Dimensions (hwd / in.)	1.50 x 3.70 x 4.50
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30
Unit Packaging Type	Box
Unit Weight (kg)	0.03
Unit Weight (lbs.)	0.07
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	14 to 131 F (-10 to 55 C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	1.7 BTU/Hr
Power Consumption (Watts)	0.5
CONNECTIONS	
Ports	1
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	DB9 (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH, WEEE
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U209-18N-NULL](#)