



L60 Series 0.230" (5.9mm) Watertight LED Panel Mount Indicator



L60 Series offers a robust body with drip-proof protection in a small package

Application

- Automotive
- Aerospace
- Industrial
- Medical
- Mining
- Military Instrumentation
- Safety and Emergency
- Transportation
- Vending and Gaming Machines


Key Features

- Watertight
- Tinted diffused LEDs
- Reflective chrome-plated body
- 45° viewing angle
- Maximum panel thickness 0.070" (1.7mm)
- Mounting hardware provided
- 6" (152.4mm) wire leads, 24 AWG
- Mounting hole 0.232" \pm 0.003" (5.9mm \pm 0.1mm)
- Operating Temperature: -20 °C to +100 °C
- Storage Temperature: -40 °C to +100 °C
- RoHS compliant

Product Dimensions

Part Numbers	Output Color	Design Voltage/ Current (Vf/If)	Max Voltage/ Current (Vf/If)	Typical Intensity (mcd)	Peak Wavelength (nm)
L60D-R5-W	Red	5VDC / 17mA	5.5VDC / 20mA	60	635
L60D-A5-W	Amber	5VDC / 17mA	5.5VDC / 20mA	30	583
L60D-G5-W	Green	5VDC / 17mA	5.5VDC / 20mA	44	565
L60D-R12-W	Red	12VDC / 16mA	14VDC / 19mA	60	635
L60D-A12-W	Amber	12VDC / 16mA	14VDC / 19mA	30	583
L60D-G12-W	Green	12VDC / 16mA	14VDC / 19mA	44	565
L60D-R28-W	Red	28VDC / 15.8mA	30VDC / 17.5mA	60	635
L60D-A28-W	Amber	28VDC / 15.8mA	30VDC / 17.5mA	30	583
L60D-G28-W	Green	28VDC / 15.8mA	30VDC / 17.5mA	44	565

Product Dimensions



Notes:

All dimensions are in inches [mm]

Compliances and Approvals

