

RECEPTACLE

SERIES
WTBT Receptacle, right angle, with mounting ears

SIZE
XX Number of contacts (10, 14, 20, 24, 26, 30, 36, 40, 44, 50, 54, 56, 60, 66, or 70)

CONTACTS

TYPE CONTACTS/TERMINATIONS:
 SARC Socket, right angle, solder cup (.035" I.D.)
 SAR7 Socket, right angle, dip solder, .109" x .025" dia
 SAR9 Socket, right angle, dip solder, .140" x .025" dia
 SAR11 Socket, right angle, dip solder, .172" x .025" dia


HARDWARE

SY Guide set
 J Fixed jackset
 JT Turning jackset, .475"
 JTA Turning jackset, .175"
 JTB Hex turning jackset, .175"
 JTC Hex turning jackset, .475"
 JTL Turning jackset, long, .675"

- WTBT connectors with "J" hardware will mate with: WTA****JT
 WTA****JTA
- WTBT connectors with "SY" hardware will mate with: WTB****SY
 WTAV****SY
- For polarized "D" shaped guides, add dash and code number to the part number (example: -7).
 See "Polarization" in Accessories section for codes.

OPTIONS

- Option Codes: Add to the end of the part number. Example: WTBT10SAR9J-D01. Call factory for additional codes.
 - 342 Remove mounting ears (.250" each end)
 - D01 Pretinned contact terminations (except solder cups, wire wraps[®] and flex contacts) with 63/37 or 60/40 solder.
 - P39 Pretinned contact terminations (except solder cups, wire wraps[®] and flex contacts) with SAC305 solder (lead free).
- = Option not RoHS compliant



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AirBorn:

[WTBT44SAR9SY](#) [WTBT70SAR9SY](#) [WTBT10SAR9SY](#) [WTBT36SAR9SY](#) [WTBT40SAR9SY](#) [WTBT60SAR9SY](#)
[WTBT30SAR9SY](#) [WTBT10SAR9JTB](#) [WTBT10SARCJTB](#) [WTBT10SARCSY](#) [WTBT14SAR9JTB](#) [WTBT14SAR9SY](#)
[WTBT14SARCJTB](#) [WTBT66SARCJTB](#) [WTBT66SARCSY](#) [WTBT70SAR9JTB](#) [WTBT70SARCJTB](#) [WTBT70SARCSY](#)
[WTBT56SARCSY](#) [WTBT60SAR9JTB](#) [WTBT60SARCJTB](#) [WTBT60SARCSY](#) [WTBT66SAR9JTB](#) [WTBT66SAR9SY](#)
[WTBT54SAR9SY](#) [WTBT54SARCJTB](#) [WTBT54SARCSY](#) [WTBT56SAR9JTB](#) [WTBT56SAR9SY](#) [WTBT56SARCJTB](#)
[WTBT44SARCSY](#) [WTBT50SAR9JTB](#) [WTBT50SAR9SY](#) [WTBT50SARCJTB](#) [WTBT50SARCSY](#) [WTBT54SAR9JTB](#)
[WTBT36SARCSY](#) [WTBT40SAR9JTB](#) [WTBT40SARCJTB](#) [WTBT40SARCSY](#) [WTBT44SAR9JTB](#) [WTBT44SARCJTB](#)
[WTBT26SARCSY](#) [WTBT30SAR9JTB](#) [WTBT30SARCJTB](#) [WTBT30SARCSY](#) [WTBT36SAR9JTB](#) [WTBT36SARCJTB](#)
[WTBT24SAR9SY](#) [WTBT24SARCJTB](#) [WTBT24SARCSY](#) [WTBT26SAR9JTB](#) [WTBT26SAR9SY](#) [WTBT26SARCJTB](#)
[WTBT14SARCSY](#) [WTBT20SAR9JTB](#) [WTBT20SAR9SY](#) [WTBT20SARCJTB](#) [WTBT20SARCSY](#) [WTBT24SAR9JTB](#)
[WTBT14SER11J](#)