

**PLUG:** NK-2K2-025-125-JC00  
**RECEPTACLE:** NM-222-025-261-THAC  
 XX-XXX-XXX-XXX-XXXX-XXX

PLUG

RECEPTACLE

**SERIES**

NK .025" Metal PC Board Mounted Connector | NM .025" Metal I/O Connector

**BODY**

2	2-Row	2	2-Row
K	BODY STYLE: Plug, vertical SMT w/ mounting ears	2	BODY STYLE: Receptacle, straight
2	BODY MATERIAL: Liquid Crystal Polymer w/ electroless nickel shell	2	BODY MATERIAL: Liquid Crystal Polymer w/ electroless nickel shell
3	BODY MATERIAL: Liquid Crystal Polymer w/ electrodeposited cadmium shell <input checked="" type="checkbox"/>	3	BODY MATERIAL: Liquid Crystal Polymer w/ electrodeposited cadmium shell <input checked="" type="checkbox"/>

**SIZE**

XXX Number of contacts (009, 015, 021, 025, 031, 037, 051, 065, 069 or 085) | XXX Number of contacts (009, 015, 021, 025, 031, 037, 051, 065, 069 or 085)

**CONTACTS**

12	TYPE CONTACTS/TERMINATIONS: Pin, SMT (.020 lead envelope)	26	TYPE CONTACTS/TERMINATIONS: Socket, straight, crimped wire
5	PLATING OPTIONS: 50 u" Au contacts; Sn/Pb alloy terminations <input checked="" type="checkbox"/>	1	PLATING OPTIONS: 50 u" Au contacts
8	50 u" Au contacts; Tin plated terminations		

**HARDWARE**

00	STYLE OF HARDWARE: None	00	STYLE OF HARDWARE: None
JC	Turning jackscrews, captivated #0-80 UNF*	TH	Threaded hole, #0-80 UNF*
00	WIRING OPTIONS: None	XX	WIRING OPTIONS: See wiring codes, Page NA-2

**OPTIONS**

010 .040 lead envelope

\* = #2-56 UNC thread on 85 position connectors  
 .050 hex key (#0-80 thread)  
 1/16" hex key (#2-56 thread)  
 Recommended torque value 1.0 inch-lbs. max. (#0-80 thread)  
 Recommended torque value 2.0 inch-lbs. max. (#2-56 thread)  
 Ball end hex wrench not recommended  
 Hex wrench key/bit conforming to the requirements of ASME / ANSI-B-18.3 is recommended.  
 .050" hex L-key long arm wrench - order AirBorn p/n CDG14148.  
 1/16" hex L-key long arm wrench - order AirBorn p/n CDG14160.

= Option not RoHS compliant

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AirBorn:](#)

[NK-2K2-037-125-JC00](#) [NK-2K2-065-125-JC00](#) [NK-2K2-015-125-JC00](#) [NK-2K2-051-125-JC00](#) [NK-2K2-021-125-JC00](#) [NK-2K2-037-125-JC00-010](#)