


55 Sockets

AS-drive HPQ

DIN 3124/ISO 2725-1, ASME B 107.5 M, AS drive and HPQ high performance steel up to size 38, chrome plated.




Code	Ø mm	d ₁ mm	d ₂ mm	d ₃ mm	L mm	t ₁ mm	t ₂ mm	Δg	g	☐
05010019	19	28.5	34.7	17	50	16	26	183	5	
05010021	21	31	34.7	18	50	16	26	226	5	
05010022	22	32	34.7	19	51	17	25.2	199	5	
05010023	23*	33.5	34.7	20	51	17	24.9	206	5	
05010024	24	34	34.7	21	51	18.5	24.6	200	5	
05010027	27	38.5	38	24	54	20	26.8	263	5	
05010030	30	42	38	27	58	21	33.6	313	5	
05010032	32	44.5	38	29	58	22	33	326	2	
05010033	33	46	40	30	60	22	34.7	372	2	
05010034	34	47	40	31	60	24	34.4	363	2	
05010036	36	49.5	40	33	60	24	33.9	386	2	
05010038	38	52	40	35	64	30	37.3	429	2	
05010041	41	55.5	40	33	67	30	37.5	498	2	
05010046	46	61	40	33	73	34	43.5	625	1	
05010050	50	66	40	33	80	34	48.5	769	1	
05010055	55	72	45	33	80	36	49.5	954	1	
05010060	60	78	45	33	80	40	50.5	1091	1	

* to be discontinued

55a Sockets

AS-drive HPQ

SAE AS 954-E (test loads), ASME B 107.1, AS drive and HPQ high performance steel up to size 1 1/2", chrome plated.




Code	Ø"	d ₁ mm	d ₂ mm	d ₃ mm	L mm	t ₁ mm	t ₂ mm	Δg	g	☐
05410040	3/4	28.5	34.7	18.6	50	16	26	176	2	
05410042	13/16	31	34.7	19.4	51	16.5	25.1	190	2	
05410044	7/8	33	34.7	21	51	18	24.5	240	2	
05410046	15/16	34	34.7	22.5	51	18.5	24.2	248	2	
05410048	1	37	38	24	52	20	24.8	251	2	
05410050	1 1/16	38.5	38	26	54	20	26.2	265	2	
05410052	1 1/8	41	38	27.5	57	20	32.5	297	2	
05410056	1 1/4	44.5	38	30.5	58	22	32.6	339	2	
05410058	1 5/16	46.5	40	32.1	59	24	33.1	368	2	
05410060	1 3/8	48.5	40	33.7	59	24	32.7	375	2	
05410062	1 7/16	50	40	35.3	60	27	33.2	395	2	
05410064	1 1/2	52	40.5	36.8	64	30	36.8	415	2	
05410066	1 5/8	56	40	33	67	30	37.5	469	1	
05410067	1 11/16	58	40	33	70	32	40.5	524	1	
05410068	1 3/4	59.5	40	33	70	32	40.5	524	1	
05410069	1 13/16	61.5	40	33	73	34	43.5	585	1	
05410070	1 7/8	63.5	40	33	76	34	45	651	1	
05410072	2	67	40	33	80	34	48.5	757	1	
05410075	2 3/16*	73	45	33	80	36	49.5	901	1	

* to be discontinued

56 Sockets

AS-drive HPQ


DIN 3124/ISO 2725-1, ASME B 107.5 M, extra deep, AS drive and HPQ high performance steel up to size 36, chrome plated.



Code	Ø mm	d ₁ mm	d ₂ mm	d ₃ mm	L mm	t ₁ mm	t ₂ mm	Δg	g	☐
05020022	22	32	34.7	19	90	40	64.2	374	5	
05020024	24	34	34.7	21	90	40	63.6	341	5	
05020027	27	38.5	38	24	90	40	62.8	443	5	
05020030	30	42	38	27	90	40	65.6	477	5	
05020032	32	44.5	38	29	90	40	65	526	2	
05020034	34	47	40	31	90	40	64.4	562	2	
05020036	36	49.5	40	33	90	40	63.9	620	2	
05020041	41	55.5	40	38	90	40	58.5	714	2	

59 INHEX sockets


for socket head screws, DIN 7422, Chrome Alloy Steel, chrome plated.



Code	mm	L ₁ mm	L ₂ mm	d mm	Δg	g	☐
05050014	14	80	25	34.7	272	1	
05050017	17	80	25	34.7	311	1	
05050019	19	80	25	34.7	346	1	
05050022	22	80	25	40	515	1	

59X Screwdriver sockets

for trisquare socket head screws (XZN[®]), Chrome Alloy Steel, chrome plated.



Code	size	L ₁ mm	L ₂ mm	d mm	Δg	g	☐
05060014	M14	90	35	34.7	281	1	
05060016	M16	80	25	34.7	302	1	
05060018	M18	100	45	34.7	310	1	

Application: Flywheel and oscillation damper on Mercedes-Benz commercial vehicles



59TX Screwdriver sockets

for inside TORX® screws, Chrome Alloy Steel, chrome plated.



Code	size	mm	L ₁ mm	L ₂ mm	d mm	Δ g	g	☐
05 10 00 60	T60	13.2	80	25	34.7	265	1	
05 10 00 70	T70	15.5	80	25	34.7	285	1	
05 10 00 80	T80	17.6	80	25	34.7	300	1	
05 10 00 90	T90	19.9	80	25	34.7	331	1	
05 10 01 00	T100	22.1	80	25	40	474	1	

Application: size T80 for MAN series M, size T100 for MAN series F

556 Sliding head

without Bar handle No 558.



Code	L mm	d mm	Δ g	☐
15070000	61.5	40	318	5


558 Bar handle



Code	L mm	d mm	Δ g	☐
15170000	510	20	1259	2

559 Extensions

DIN 3123/ISO 3316.



Code	size	L mm	d mm	Δ g	☐
15010003	4	95	35	369	5
15010001	8	200	35	696	5
15010002	16	400	35	1255	5

561 Universal joint

DIN 3123/ISO 3316.



Code	L mm	d mm	Δ g	☐
15020000	109	40	566	1

568 Adaptor



3/4" socket x 1/2" plug (20 x 12.5), maximum torque 512 N m, DIN 3123/ISO 3316, HPQ high performance steel.



Code	L mm	d mm	Δ g	☐
15030003	55	34.7	203	5

569 Adaptor



3/4" inside x 1" plug (20 x 25), DIN 3123/ISO 3316, HPQ high performance steel.



Code	L mm	d mm	Δ g	☐
15030006	61	34.7	295	5

3

Drive tools and accessories

3/4" □, finish: Chrome Alloy Steel, chrome plated.



552 Ratchet



reversible, 36 teeth, with QuickRelease safety lock, without Bar Handle No 558.



Code	L mm	b mm	a mm	Δ g	☐
15110000	165	70	55	1684	1

5520 Spare parts set for ratchet No 552

Content: 1 pinion, 1 pawl, 1 lever, 1 ball, 1 compression spring, 2 screws

Code	Δ g	☐
19050000	536	1

563 Ratchet adaptor

reversible, 44 teeth.



Code	L mm	∅ mm	Δ g	☐
15140000	105.5	63	1257	1

554 Flexible head



with QuickRelease safety lock, without Bar handle No 558.



Code	L mm	d mm	Δ g	☐
15060000	132	40	612	5