



datasheet for MKU 1
 article number: 930320100



product description:	order number: 930 320-100
description:	2 mm diameter miniature coupling, insulated, nickel-plated copper beryllium contact (spring-loaded) with solder connection. Flexible, shatter-proof insulated sleeve. For making up connecting leads with a maximum external diameter of 2 mm.
typ:	MKU 1 schwarz/black
system:	2mm system
order number:	930 320-100
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
norm	IEC 61010
type of contact:	2 mm socket (spring-loaded)
type of termination:	solder
rated voltage:	30 VAC / 60 VDC
rated current:	6 A
Please consider derating curve!	
contact resistance:	6 mOhm
material	
contact material:	contact spring: copper - beryllium
contact surface material:	tin
housing material:	PVC - P
environmental conditions:	
temperature range:	-20 °C to +60 °C
drawing	
	