


- NOTES:
- 1) 18/2 SVO 90C BLACK WITH 41X34 BARE COPPER STRANDING.
 - 2) CONDUCTOR COLORS: BLACK AND WHITE.
 - 3) 300 VOLTS/10 AMP MAX.
 - 4) APPROVALS: UL & CSA
 - 5) CORDAGE D.D. : .260" (REF.)
 - 6) 100 CORDS/CARTON
 - 7) CORD SET LABEL HAS VOLEX LOGO AND PART NUMBER.
 - 8) PRODUCT IS ROHS & PROP 65 COMPLIANT
 - 9) ALL DIMENSIONS IN INCHES UNLESS OTHERWISE NOTED.

REV	DESCRIPTION	DATE
1	FIRST ISSUE	8/10/07

<input checked="" type="checkbox"/> Indianapolis, IN <input type="checkbox"/> Conover, N.C. <input type="checkbox"/> Freemont, CA <input type="checkbox"/> Aguascalientes, MX <input type="checkbox"/> Tijuana, Mexico <input type="checkbox"/> Hermosillo, MX <input type="checkbox"/> Clinton, AR <input type="checkbox"/> Kanata, Canada	Proprietary Notice: This document is the property of Volex Incorporated. The information contained herein is not to be disclosed to anyone without the express written consent of Volex Inc.	MATERIAL:	FINISH:	TOLERANCE UNLESS OTHERWISE SPECIFIED .XXX ± .005 .XX ± .02 .X ± .03 FRACT. ± 1/32° ANGULAR ± 1/2°	ITEM DESCRIPTION		
		JACKET: SMOOTH	SCALE: NDT TO SCALE		ECD: N/A	APPROVED	DRAWN BY
 CUD FORM IN71-07 REV.A		APPROVED: MAF PART NO. 6601		DRAWN BY: MAF DATE: 8/10/07			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Volex:](#)

[6601](#)