


# 5G MOBILE MAGNETIC SMA ANTENNA



**PARAMETER**

**RATED VALUE**

Frequency Range	617-960, 1400-2690, 3300-5900 MHz
Polarization	Linear
Radiation pattern type	Omnidirectional
Gain	3.6 dBi
VSWR	3.5
Impedance	50 Ω
Maximum power	20 W
Cable	RG-58, 3 m
Connector	SMA Male
Operating Temperature	-20 °C +65 °C
Mounting Method	Magnet
IP rating	IP33
Weight	150 g
RoHS compliant	✓



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Teltonika:](#)

[PR1KS536](#)