

Datasheet

Hexagon Plug, 1-1/2"



RS Stock number 499-3669




Standard Pattern

| SIZE | 1/8" | | 1/4" | | 3/8" | | 1/2" | | 3/4" | | 1" | | 1-1/4" | | 1-1/2" | | 2" | | 2-1/2" | | 3" | | 4" | |
|------|------|------|------|------|------|------|------|------|------|------|------|------|--------|------|--------|------|------|------|--------|------|------|------|-------|------|
| | mm | in | mm | in | mm | in | mm | in | mm | in | mm | in | mm | in | mm | in | mm | in | mm | in | mm | in | mm | in |
| H | 10.5 | 0.41 | 12 | 0.47 | 13.5 | 0.53 | 16 | 0.63 | 16.5 | 0.65 | 19 | 0.75 | 21 | 0.83 | 21 | 0.83 | 22.8 | 0.9 | 29 | 1.14 | 29.3 | 1.15 | 30.8 | 1.21 |
| L | 16.2 | 0.64 | 18 | 0.71 | 19.5 | 0.77 | 22.6 | 0.89 | 23.3 | 0.92 | 26.8 | 1.06 | 30.5 | 1.2 | 30.8 | 1.21 | 34 | 1.34 | 40.5 | 1.59 | 41.7 | 1.64 | 44.8 | 1.76 |
| W | 13.2 | 0.52 | 16.6 | 0.65 | 19.3 | 0.76 | 25.2 | 0.99 | 29.7 | 1.17 | 36.5 | 1.44 | 45.3 | 1.78 | 51.4 | 2.02 | 62.5 | 2.46 | 79.5 | 3.13 | 92 | 3.62 | 117.5 | 4.63 |

Tolerance: $\pm 0.5\text{mm}$ (1/8"~2")
 $\pm 0.8\text{mm}$ (2-1/2"~4")



1/8"~2"



2-1/2"~4"