


REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	YCh 09/04/10'	~	



Housing with contact

Upper shell



NOTES:

- SPECIFICATIONS:
 - CONTACT RESISTANCE: 30mΩ(max.) INITIAL FOR VBUS AND GND CONTACTS. 50mΩ(max.) INITIAL FOR ALL OTHER CONTACTS.
 - INSULATOR RESISTANCE: 100MΩ min. AT 100V DC.
 - CURRENT RATING: 1.8A FOR VBUS PIN AND ITS CORESPONDING GND PIN. 0.25A (MIN.) FOR ALL OTHER CONTACTS
 - VOLTAGE RATING: 30V AC/DC.
 - DIELECTRIC STRENGTH: AC 100V FOR 1 Minute.
 - OPERATING TEMPERATURE: -55°C ~ +85°C.


2. MATERIALS:

- HOUSING: THERMOPLASTIC (UL 94-0).
- CONTACT: COPPER ALLOY
- SHELL: COPPER ALLOY.

3. PRODUCT NUMBER CODE:

DS1107-01 - X X X

- CONTACT PLATED:
 - 0: Selective Gold Flash
 - C: 3u" Gold
 - 3: 30u" Gold
- SHELL PLATED:
 - N: Nickel
 - 6: Tin
- COLOR OF HOUSING:
 - L: Blue
 - W: White
 - B: Black



Down shell

Tel:86-574-63508787
 Fax:86-574-63510817
 E-mail:sale@zhenqin.com.cn
 Http://www.connfly.com

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	USB 3.0 PLUG A TYPE	
X.	±0.60	X.	±5°	UNITS	mm		MALE SOLDER TYPE	
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1107-01	
.XX	±0.25	.XX	±2°					
DRAWING TYPE		CUSTOMER				晨翔电子有限公司		
SCALE		1:1	SHEET	1 OF 1		CONNFLY CONNFLY ELECTRONIC CO. LTD		
DRAWING NO.		C-DS1107-01-XXX						