


Item no.: 236-412
 Product description: PCB TERMINAL STRIP; 2 SOLDER PINS / POLE; 12 POLE;
 PIN SPACING 5/5.08 MM / 0.2 IN; FRONT-/SIDE-ENTRY;
 CAGE CLAMP®CONNECTION



Packing unit 80 4*20 pieces

Pin spacing from	5 mm
Pin spacing up to	5.08 mm
Pin spacing from	0.197 in
Pin spacing up to	0.2 in
pole count	12
Cross section from [mm²]	0.08 mm²
Cross section to [mm²]	2.5 mm²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	12 AWG
Connection method	CAGE CLAMP® CONNECTION
Voltage CSA	300 V
Voltage UL	300 V
Current rating UL	15 A
Current rating CSA	15 A
Measured voltage EN	250 V
Measured shock voltage	4 kV
Pollution degree	3
Current intensity EN	16 A
Measured voltage EN	500 V
Measured shock voltage	4 kV
Pollution degree	2
Current intensity EN	16 A



Color	gray
Wiring type	Front-/Side-entry
No. of connection Points	12
No. of potentials	12
Height	13 mm
Height	0.512 in
Width	62.3 mm
Width	2.453 in
Depth	14 mm
Depth	0.551 in
Strip length from	5 mm
Strip length to	6 mm
Strip length	0.22 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
236-412	BBJ	B/12/697/03	250	16	0,5-2,5
236-412	BV	11915/A0	500/250	16	0,08-2,5
236-412	CCA	DK2082	250	16	0,5-2,5
236-412	CSA	154112-1673957	300	15	28-12
236-412	CSM	017956	250	16	0,08-2,5
236-412	DEMKO	98-04355	250	16	0,5-2,5
236-412	DNV	E7569	250	16	0,5-2,5
236-412	GL	17296-00HH	500/250	16	0,5-2,5
236-412	KEMA	83.6970.01/02	380	16	2,5
236-412	NEMKO	M58459/01	50		2,5
236-412	RMR	11130002	250	16	0,5-2,5
236-412	RosTesT	B09523	250	16	0,08-2,5
236-412	SEMKO	9411003	400		2,5
236-412	UL	E45172	300	15	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected