

- Products**
- Product On-Line Catalog
 - Product Search**
 - Evaluate
 - FAQs
 - Product Bulletins
 - PDF-Harness Boar ..
 - Design a Solution
 - Catalog Cut Sheet
 - PDF-WBH-EB-C Pro
 - Part Drawings
 - PDF-Harness Boar
 - How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Product Search >

Current refinements (click to remove) Search Tips [?](#)

Part Number > HBN3-T

Your search criteria matched only one product, shown below

HBN3-T



- Speeds routing of wires
- Uniform driving depth is insured by a collar stop
- Smooth finish on nails prevents abrasion on wire jackets

Part Number	HBN3-T
RoHS Compliance Status	RoHS directive is not applicable
Part Description	Harness Board Nail
Product Type	Harness Board Accessories
Material	Nickel Plated Steel
Color	Steel
Diameter (In.)	0.122
Diameter (mm)	3.1
Length (In.)	3.00
Length (mm)	76.2
CE Compliant	No
Environment	Indoor
Mounting Method	Nail
Overall Length (In.)	3.67
Overall Length (mm)	93.2
Pricing Description	Harness Board Nail, Standard, 3.0" (76.2mm)
Thickness (In.)	.12
Thickness (mm)	3.0
Type	Harness Board Fixtures
Min. Order UOM	PC
Min. Order Qty.	200
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.