

0 601 9H4 100 – GSR 18V-28

Material number	0 601 9H4 100	0 601 9H4 171
EAN	3165140940757	3165140940719
2 x battery GBA 18V 5.0Ah 1 600 A00 2U5		✓
Cardboard box	✓	
L-BOXX 136 1 600 A01 2G0		✓
L-BOXX inlay for tool and charger		✓
Quick charger AL 1860 CV 2 607 225 323		✓
Tool dimensions (height)	230 mm	248 mm
Packaging dimensions (width x length x height)	250 x 325 x 110 mm	350 x 440 x 155 mm
Battery voltage	18.0 V	18.0 V
Battery capacity		5,0 Ah

Technical data

Technical data

Torque (soft/hard/max.)	28/63/- Nm
No-load speed (1st gear / 2nd gear)	0 – 500 / 0 – 1,900 rpm
Chuck capacity, min./max.	1.5 / 13 mm
Battery voltage	18 V
Weight excl. battery	1.1 kg
Torque settings	20+1

Drilling diameter


Max. drilling diameter in wood	38 mm
Max. drilling diameter in steel	13 mm

Screw diameter

Max. screw diameter	8 mm
---------------------	------

Noise/vibration information

Sound pressure level	70 dB(A)
Uncertainty K	3 dB



Sales information

Positioning

- Durable all-rounder in a compact format

User benefit

- Durable: Less wear thanks to 13 mm full metal chuck
- Long-lasting: Reduced risk of motor overload and long lifetime thanks to Electronic Motor Protection (EMP)
- Ergonomic: Comfortable handling due to the compact design

