

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0502179001**
Status: **Active**
Overview: Mighty-SPOX Connector System
Description: Mighty-SPOX Crimp Terminal, 3.50mm Pitch, 18-24 AWG, Reel, Brass

Documents:

3D Model	Product Specification PS-51067-016 (PDF)
3D Model (PDF)	Product Specification PS-51067-017 (PDF)
Drawing (PDF)	Product Specification PS-51067-019-001 (PDF)
Product Specification PS-51067-001-001 (PDF)	Product Specification PS-51067-020-001 (PDF)
Product Specification PS-51067-002-001 (PDF)	Product Specification PS-51067-021-001 (PDF)
Product Specification PS-51067-005 (PDF)	Packaging Specification 502179200-200 (PDF)
Product Specification PS-51067-007 (PDF)	Packaging Specification SPK-50217-001-001 (PDF)
Product Specification PS-51067-008 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	50217
Application	Signal, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<u>Mighty-SPOX Connector System</u>
Packaging Alternative	502179101 (Loose)
Product Name	Mighty-SPOX
UPC	800753630277


Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	238.300/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40-3.00mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm ²	N/A

Material Info

Reference - Drawing Numbers

Crimp Specification	CS-50217_50539
Packaging Specification	502179200-200, SPK-50217-001-001
Product Specification	PS-51067-001-001, PS-51067-002-001, PS-51067-005, PS-51067-007, PS-51067-008, PS-51067-016, PS-51067-017, PS-51067-019-001, PS-51067-020-001, PS-51067-021-001
Sales Drawing	SD-50217-XXXX



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

50217 Series

Mates With

50419

Use With

51067

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool, UL Approved	638118300
Extraction and Activation Tool	638132700
T2 Terminator Die, Large Insulation	638503000
T2 Terminator Die, Small Insulation	638503100

FineAdjust	<u>638603000</u>
Applicator, Large	
Insulation	
FineAdjust	<u>638603100</u>
Applicator, Small	
Insulation	

Japan

Description	Product #
--------------------	------------------

Applicator for M211A	<u>571833000</u>
----------------------	------------------

Bench Press, 18-24

AWG Wire

S-1 Applicator for	<u>571833700</u>
--------------------	------------------

3.50mm Pitch Crimp

Terminal, 18-24

AWG, UL1007 Wires

S-1 Applicator for	<u>571833710</u>
--------------------	------------------

3.50mm Pitch Crimp

Terminal, 18-24

AWG, UL1015 Wires

This document was generated on 02/18/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION