

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0039000090**  
**Status:** **Active**  
**Overview:** Mini-Fit Jr. Power Connectors  
**Description:** Mini-Fit Female Crimp Terminal, Gold (Au) over Brass, 16 AWG, Bag

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-58696-004-001 (PDF)</a>
<a href="#">Product Specification PS-5556-001-001 (PDF)</a>	<a href="#">Packaging Specification PK-5556-003 (PDF)</a>
<a href="#">Product Specification PS-5556-002-001 (PDF)</a>	<a href="#">Test Summary 55560010-TS-000 (PDF)</a>
<a href="#">Product Specification PS-58691-004-001 (PDF)</a>	<a href="#">Test Summary TS-5556-002-001 (PDF)</a>
<a href="#">Application Specification 55560001-AS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**General**

Product Family	Crimp Terminals
Series	5556
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Fit Jr. Power Connectors</a>
Packaging Alternative	<a href="#">39000089 (Reel)</a>
Product Name	Mini-Fit
UPC	800754394956

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	130.000/mg
Packaging Type	Bag
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	16
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

**Material Info**

Engineering Number	5556GS3L
--------------------	----------

**Reference - Drawing Numbers**

Application Specification	55560001-AS-000, AS-58696-004-001
Packaging Specification	PK-5556-003
Product Specification	PS-5556-001-001, PS-5556-002-001, PS-58691-004-001
Sales Drawing	SD-5556-006-001
Test Summary	55560010-TS-000, TS-5556-002-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per -  
ECHA\_01\_2020 (16  
January 2020

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[5556 Series](#)

**Use With**

Mini-Fit Jr. Receptacle Housing [5557](#)  
 <br>Mini-Fit BMI Slide and Lock Panel  
 Mount [44516](#) <br>Mini-Fit BMI Panel Mount  
 Receptacle Housing<br> [42474](#) , [43760](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool	<a href="#">11030044</a>
Hand Crimp Tool for Mini-Fit Jr. Male and Female Crimp Terminals, 16 AWG	<a href="#">2002182200</a>

**Japan**

**Description**

**Product #**

Hand Crimp Tool	<a href="#">570225300</a>
-----------------	---------------------------

This document was generated on 03/04/2020

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**