




# SLIM USB-C Female-Male FRONT MOUNTING FEEDTHROUGH CONNECTOR



### VARIANTS

Part No.

**CP30611**

SLIM FM USB-C F-M Black plastic frame, CSK holes

**CP30611X**

SLIM FM USB-C F-M Black plastic frame, Ø2.5 PLAIN holes

**CP30611X1**

SLIM FM USB-C F-M Black plastic frame, Ø3.2 PLAIN holes

### Feedthrough Features

- Fits standard rectangular cutout.
- Various hole mounting options.
- No soldering or punch termination. Use standard cable for each connector style.
- Low rear profile.

### General:

Please note: Functionality is affected by cable quality, length and cable wiring configuration.

### Material:

1. Insert: ABS - UL94 HB
2. Plastic Frame: Polyamide UL94 V-2

### USB-C Specification:

Maximum Rated Current - 3A  
 Maximum Working Voltage - 30V  
 Withstanding Voltage - 100V for 1 minute.  
 Contact Resistance - 40 Milli-ohms Max.  
 Insulation Resistance - 100 Mega-ohms Min.  
 Insulator Flammability Rating - UL-94V0  
 Insertion Life - 10,000 Cycles.