

LED W 2 x 4.6d superbright, white, 24 V

1.90.690.365/0000



Electrical characteristics of LED

Max. current, I_F	12 mA
LED wavelength typ.	630
Forward voltage typ. U_F at I_F	24
LED breakdown voltage U_R bei I_F	24
Light intensity	400

Other specifications

Socket	W 2 x 4.6d
Color	white
Ambient temp. operating min.	-30 °C
Ambient temp. operating max.	+65 °C
Storage temperature min.	-35 °C
Storage temperature max.	+100 °C
ROHS compliant	yes
REACH compliant	yes

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

RAFI:

[1.90.690.365/0000](https://www.mouser.com/RFI/1.90.690.365/0000)