



Quality Products. Service Excellence.

Utility Enclosures 1411-1412 Series

Key Features:

Two Versions:

- "1411" series - 0.04" thick aluminum (26 sizes)
- "1412" series - 20 gauge steel (8 sizes).
- Four self-tapping screws included.

Features:

- Versions without mounting flanges are available in unfinished aluminum or smooth ASA 61 grey powder coat (Hammond color GY2)
- Versions with wall-mounting flanges are available in unfinished aluminum or smooth black powder coat (Hammond color BK2)
- Unpainted aluminum version is protected through manufacturing and shipping with a plastic film cover to ensure a high quality finish. Also doubles as a removable drilling template.
- Steel finished in ASA 61 grey baked powder paint (inside and out to prevent rust).
- Replacement screws **1421J6** (Pkg. of six (6), 6-32 Philips head screws).



Photo Features:



Unfinished aluminum versions have protective wrapping to maintain high quality finish.

Standard versions are available unfinished or powder coated gray. Steel version available only in gray.

Flanged aluminum versions available unfinished or powder coated in smooth black.

Accessories

- Sheet Metal Screws

Enclosures

| Aluminum Gray | Aluminum Unfinished | Aluminum Black w/ Flanges | Aluminum Unfinished w/ Flanges | Steel Gray | Length | Width | Height |
|------------------|------------------------|------------------------------|-----------------------------------|---------------|--------|-------|--------|
| 1411B | 1411BU | 1411FBGBK | 1411FBBU | | 2.70 | 2.20 | 1.60 |
| 1411C | 1411CU | 1411FBCBK | 1411FBCU | | 3.20 | 2.20 | 1.10 |
| 1411D | 1411DU | 1411FBDBK | 1411FBDU | | 3.20 | 2.20 | 1.60 |
| 1411G | 1411GU | 1411FBGBK | 1411FBGU | | 4.00 | 2.20 | 1.60 |
| 1411H | 1411HU | 1411FBHBK | 1411FBHU | | 4.00 | 2.20 | 2.20 |
| 1411F | 1411FU | 1411FBFBK | 1411FBFU | | 4.00 | 2.20 | 3.00 |
| 1411J | 1411JU | | | 1412J | 4.00 | 4.00 | 2.00 |
| 1411K | 1411KU | 1411FBK BK | 1411FBKU | | 5.00 | 2.20 | 2.20 |
| 1411N | 1411NU | 1411FBNBK | 1411FBNU | | 5.00 | 3.00 | 2.20 |
| 1411L | 1411LU | 1411FBLBK | 1411FBLU | | 5.00 | 4.00 | 3.00 |
| 1411M | 1411MU | | | | 6.00 | 3.00 | 3.00 |
| 1411PP | 1411PPU | | | 1412PP | 6.00 | 4.00 | 2.00 |
| 1411P | 1411PU | 1411FBPBK | 1411FBPU | | 6.00 | 5.00 | 4.00 |
| 1411Q | 1411QU | 1411FBQBK | 1411FBQU | | 7.00 | 5.00 | 3.00 |
| 1411SS | 1411SSU | | | 1412SS | 8.00 | 4.00 | 2.00 |
| 1411S | 1411SU | 1411FBSBK | 1411FBSU | | 8.00 | 4.00 | 3.00 |
| 1411RR | 1411RRU | | | 1412RR | 8.00 | 6.00 | 2.00 |
| 1411R | 1411RU | 1411FBRBK | 1411FBRU | | 8.00 | 6.00 | 3.50 |
| 1411T | 1411TU | | | | 10.00 | 2.20 | 1.60 |
| 1411TT | 1411TTU | | | 1412TT | 10.00 | 6.00 | 2.00 |
| 1411U | 1411UU | 1411FBUBK | 1411FBUU | | 10.00 | 6.00 | 3.50 |
| 1411W | 1411WU | | | | 12.00 | 3.00 | 2.20 |
| 1411X | 1411XU | 1411FBXBK | 1411FBXU | 1412X | 12.00 | 7.00 | 4.00 |
| 1411V | 1411VU | | | 1412V | 12.00 | 8.00 | 3.00 |
| 1411Y | 1411YU | | | 1412Y | 16.00 | 8.00 | 3.00 |
| 1411Z | 1411ZU | | | | 17.00 | 5.00 | 4.00 |

Data subject to change without notice

© 2022. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Hammond:

[1411HU](#) [1411DU](#) [1411NU](#) [1411TU](#) [1411XU](#) [1411LU](#) [1411PU](#) [1411ZU](#) [1411FU](#) [1411BU](#) [1411GU](#) [1411WU](#)
[1411KU](#) [1411UU](#) [1411RU](#) [1411CU](#) [1411QU](#) [1411MU](#) [1411SU](#) [1411Q](#) [1411U](#) [1411M](#) [1411R](#) [1411K](#) [1411N](#)
[1411X](#) [1411P](#) [1411D](#) [1411W](#) [1411L](#) [1411G](#) [1411F](#) [1411Z](#) [1411B](#) [1411C](#) [1411S](#) [1411T](#) [1411H](#) [1411J](#) [1411JU](#)
[1411PP](#) [1411PPU](#) [1411RR](#) [1411RRU](#) [1411SS](#) [1411SSU](#) [1411TT](#) [1411TTU](#) [1411V](#) [1411VU](#) [1411Y](#) [1411YU](#)
[1412J](#) [1412PP](#) [1412RR](#) [1412SS](#) [1412TT](#) [1412V](#) [1412X](#) [1412Y](#) [1411FBHU](#) [1411FBHBK](#) [1411FBSU](#) [1411FBSBK](#)
[1411FBDU](#) [1411FBDBK](#) [1411FBNU](#) [1411FBNBK](#) [1411FBBBK](#) [1411FBBU](#) [1411FBCU](#) [1411FBCBK](#) [1411FBLU](#)
[1411FBLBK](#) [1411FBRU](#) [1411FBRBK](#) [1411FBPU](#) [1411FBPBK](#) [1411FBFU](#) [1411FBFBK](#) [1411FBQBK](#) [1411FBQU](#)
[1411FBUU](#) [1411FBUBK](#) [1411FBKU](#) [1411FBKBK](#) [1411FBGBK](#) [1411FBGU](#) [1411FBXU](#) [1411FBXBK](#)