

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	25[mm]
Max. Air Flow:	96.4[CFM]
Max. Air Flow:	2.73[m3 per min]
Max. Static Pressure:	0.6[In H2O]
Max. Static Pressure:	150[Pa]
Fan Speed:	5600[RPM]
Noise:	51[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	14[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.38[A]
Input Power:	9.1[W]
Mass:	150[g]
IP Rating:	IP68/IP69K
Tach / Locked Rotor Output:	No
Status:	Active

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[09225VA-24Q-CA-00](#)