


Drawing For Reference Only

RoHS STANDARD



Technical requirement :

- 1 . This product should meet EU RoHS related requirement.
- 2 . The surface of plastic part should be without any crackle such as burr,lack,and so on phenomenon.
- 3 . The surface of metal part should be without any defect such as scour,nick,oxidation and plating problem.
- 4 . The electronic performance should be the same as spec.
- 5 . The un-specified tolerance is : <math> < 6 \pm 0.1 </math>
 $6 \sim 20 \pm 0.2$
 $> 20 \pm 0.3$

Specification:

Contact Resistance: 30m ohm max.
 Insulation Resistance: 100M ohm min. at DC 500V
 Dielectric Strength: AC 500V for one minute.

DCI DRAGON CITY INDUSTRIES LIMITED			DESIGN	K.W LAW	REMARK		SCALE	
			DRAWING	S.M HUNG	REMARK		MATERIAL	
PART NAME	6.3MM MONO PLUG TO 3.5 MM MONO JACK	TOLERANCE : ±	CHECK	K.L WONG	REMARK		DWG. NO.	110122-1144
PART NO.	NP-552-EN	UNIT: MM	APPROVAL	K.W CHAN	REMARK		SHEET	