


Drawing For Reference Only

RoHS STANDARD



Technical requirement :

1. This product should meet EU RoHS related requirement.
2. The surface of plastic part should be without any crackle such as burr,lack,and so on phenomenon.
3. The surface of metal part should be without any defect such as scour,nick,oxidation and plating problem.
4. The electronic performance should be the same as spec.
5. The un-specified tolerance is : <math><6 \pm 0.1</math>  
                                   <math>6 \sim 20 \pm 0.2</math>  
                                   <math>>20 \pm 0.3</math>

Specification :

- Contact Resistance : 30m ohm max.
- Insulation Resistance : 100M ohm mih. at DC 500V
- Dielectric Strength : AC 500V for one minute.

**DCI** DRAGON CITY INDUSTRIES LIMITED

			DESIGN	K.W LAW	REMARK	SCALE	
			DRAWING	S.M HUNG	REMARK	MATERIAL	
PART NAME	2.5MM PHONE INLINE JACK MONO	TOLERANCE : ±	CHECK	K.L WONG	REMARK	DWG. NO.	110121-1442
PART NO.	NP-317-EN	UNIT: MM	APPROVAL	K.W CHAN	REMARK	SHEET	