


Наконечники на кабель



Модель	Сечение провода		L мм	C мм	D мм
	AWG	мм ²			
DN00206	24	0.25	6	0.8	1.1
DN00208	24	0.25	8	0.8	1.1
DN00306	22	0.34	6	0.8	1.1
DN00308	22	0.34	8	0.8	1.1
DN00506	20	0.5	6	1.0	1.3
DN00508	20	0.5	8	1.0	1.3
DN00510	20	0.5	10	1.0	1.3
DN00706	18	0.75	6	1.2	1.5
DN00708	18	0.75	8	1.2	1.5
DN00712	18	0.75	12	1.2	1.5
DN01006	17	1	6	1.4	1.7
DN01008	17	1	8	1.4	1.7
DN01012	17	1	12	1.4	1.7
DN01508	16	1.5	8	1.7	2.0
DN01512	16	1.5	10	1.7	2.0
DN01518	16	1.5	18	1.7	2.0
DN02508	14	2.5	8	2.3	2.6
DN02512	14	2.5	12	2.3	2.6
DN02518	14	2.5	18	2.3	2.6
DN04008	12	4	8	2.8	3.2
DN04012	12	4	12	2.8	3.2
DN04018	12	4	18	2.8	3.2
DN06012	10	6	12	3.5	3.9
DN06018	10	6	18	3.5	3.9
DN10012	7	10	12	4.5	4.9
DN10018	7	10	18	4.5	4.9
DN16012	6	16	12	5.8	6.2
DN16018	6	16	18	5.8	6.2
DN25016	3	25	16	7.5	7.9
DN25022	3	25	22	7.5	7.9
DN35016	2	35	16	8.3	8.7
DN35025	2	35	25	8.3	8.7
DN50020	1	50	20	10.3	10.9