

General purpose prototyping circuit board for analog and digital use.

Features


- A higher quality prototyping board with the traditional stripboard pattern. Tracks run the length of the board.
- StripBoard-3U uses a high-quality FR4 glass epoxy board. It has better stability and moisture resistance than boards using phenolic or SRBP (synthetic resin bonded paper) to avoid warping.
- 0.1" hole spacing for DIP integrated circuits and headers.
- Standard single height (3U) Eurocard/VME size. Many off the shelf enclosures and card cages are available.

Specifications

- Etched FR4 glass-epoxy circuit board.
- 1oz/ft² copper with an anti-tarnish coating for easy soldering.
Lead free and RoHS compatible.
- Holes are drilled on 0.1" (2.54mm) centers.
- 0.037" (0.94mm) holes sized for ICs or square post headers.
- 38 x 62 holes (38 strips)
- Size 3U = 100 x 160mm (3.9 x 6.3in),
1/16" thick (1.6mm)

Order Part# ST3U

Board Layout (actual size)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[BusBoard Prototype Systems:](#)

[ST3U](#)