

Han 1 HC-M-TC350



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 001 3001
Specification	Han 1 HC-M-TC350
HARTING eCatalogue	https://b2b.harting.com/09110013001

Identification

Category	Inserts
Series	Han [®] HC Modular
Identification	350

Version

Termination method	Crimp termination
Gender	Male
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	25 ... 120 mm ²
Wire outer diameter	≤22 mm
Rated current	350 A
Rated voltage	2,000 V
Rated impulse voltage	12 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC) Polyamide (PA)
-------------------	--------------------------------------



Pushing Performance

Material properties

Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	38 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440205 Contact insert for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09110013001](#)