

Coaxial Cable Connector 11_BNC-75-2-15/133_N

Description

Straight cable plug

Interface standards

Interface compatible with IEC 61169-8



Technical Data

Electrical Data

| | |
|--------------------------|-------|
| Impedance | 75 Ω |
| Interface frequency max. | 1 GHz |

Mechanical Data

| | |
|----------------|-----------|
| Centre contact | crimped |
| Outer contact | crimped |
| Weight | 0.0095 kg |

Environmental Data

| | |
|--|------------------|
| Operating temperature | -65 °C to 165 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|-----------------------|-----------------------------------|
| Centre contact | Bronze / Brass | Gold Plating (Nickel underplated) |
| Outer contact | Brass | SUCOPLATE (R) Plating |
| Body | Brass | SUCOPLATE (R) Plating |
| Insulator | PFA / PTFE | |
| Coupling nut | Brass | SUCOPLATE (R) Plating |
| Gasket | VMQ (Silicone rubber) | |
| Crimp ferrule | Copper | SUCOPLATE (R) Plating |

Related Documents

| | |
|----------------------|----------------|
| Outline drawing | DOU-00071335 |
| Catalogue drawing | DOU-00006199 |
| Assembly instruction | DOC-0000179123 |

Ordering Information

| | |
|----------------------|-----------------------|
| Bulk 100 pcs package | 11_BNC-75-2-15/133_NH |
| Single package | 11_BNC-75-2-15/133_NE |

Additional Information

| | |
|-----------------|------------------------|
| Suitable cables | RG_179_B/U, RG_187_A/U |
|-----------------|------------------------|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11_BNC-75-2-15/133_NH](#)