

Coaxial Cable Connector 11_QMA-50-2-2/133_N

Description

Straight cable plug

Interface standards
QMA QLF compliant



Technical Data

Electrical Data

| | |
|--------------------------|-------------|
| Impedance | 50 Ω |
| Interface frequency max. | 18 GHz |

Mechanical Data

| | |
|----------------|-----------|
| Centre contact | crimped |
| Outer contact | crimped |
| Weight | 0.0041 kg |

Environmental Data

| | |
|--|-----------------|
| Operating temperature | -40 °C to 85 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------|-----------------------|
| Centre contact | Brass | SUCOPRO Plating |
| Outer contact | Bronze | SUCOPLATE (R) Plating |
| Body | Brass | SUCOPLATE (R) Plating |
| Insulator | PFA / PTFE | |
| Crimp ferrule | Copper | SUCOPLATE (R) Plating |

Related Documents

| | |
|----------------------|----------------|
| Outline drawing | DOU-00005827 |
| Catalogue drawing | DOU-00005829 |
| Assembly instruction | DOC-0000183265 |

Ordering Information

| | |
|----------------------|----------------------|
| Bulk 100 pcs package | 11_QMA-50-2-2/133_NH |
| Single package | 11_QMA-50-2-2/133_NE |

Additional Information

| | |
|-----------------|--|
| Suitable cables | RG_316_U, ENVIROFLEX_316, RG_188_A/U, RG_174_U |
|-----------------|--|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11_QMA-50-2-2/133_NE](#)