

## Coaxial PCB Connector 82\_MCX-S50-0-29/111\_N

### Description

Straight PCB jack

Interface Standards

IEC 60169-36\_CECC 22220



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	6 GHz

#### Mechanical Data

Board mounting type	surface mount
Weight	0.0004 kg

#### Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

### Related Documents

Outline drawing	DOU-00012753
Catalogue drawing	DCA-00012755
Mounting hole	DOU-00012756

### Ordering Information

Bulk 100 pcs package	82_MCX-S50-0-29/111_NH
Tape and Reel package	82_MCX-S50-0-29/111_NM
Single package	82_MCX-S50-0-29/111_NE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[82\\_MCX-S50-0-29/111\\_NH](#)