

Coaxial PCB Connector 84_MM CX-50-0-1/111_O

Description

Right angle PCB plug

Interface Standards
SUHNER-MM CX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type through holes
Weight 0.0005 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00012883
Catalogue drawing DCA-00012885
Mounting hole DOU-00012639

Ordering Information

Bulk 100 pcs package 84_MM CX-50-0-1/111_OH

Remarks

PCB connector without stand-offs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[84_MMCX-50-0-1/111_OH](#)