



Fuse-link, low voltage, 1 A, AC 500 V, 120 kA, 10 x 38 mm, gL/gG, IEC



Part no. CYLINDRICAL FUSE 10 x 38 1A GG 500V AC
Catalog No. C10G1

EL-Nummer (Norway) 1600252

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	1
Rated voltage			AC 500 V
Size			10 x 38 mm
Utilization category			gL/gG
Breaking Capacity		kA	120
usable for size/applications			for industrial applications for general purpose use
Standard/Approval			IEC
Shape			cylindrical
Standards/Regulations			IEC 60269-2

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Cylindrical fuse (EC002704)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Cylindrical fuse (safety fuse) (ecl@ss10.0.1-27-14-20-02 [AFZ797013])			
Size			10x38 mm
Rated voltage		V	500 - 500
Rated voltage			Other
Voltage type			AC
Utilization category			gL/gG (cable protection/equipment protection)
Rated operating frequency		Hz	45 - 62
Nominal current		A	1
With striker			No
Release characteristic			Other
Breaking capacity		kA	120