


distributor block

FR-8-1/2

Part number: 6411

FESTO



Data sheet

Feature	Value
Nominal size	18.6 mm
Assembly position	Any
Operating pressure complete temperature range	0 ... 16 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
Ambient temperature	-10 ... 60 °C
Product weight	1,000 g
Number of outputs	8
Number of supply lines	1
Pneumatic connection, port 1	Female thread G3/4
Pneumatic connection, port 2	Female thread G1/2
Materials note	Conforms to RoHS
Material housing	Aluminium die cast