




REVISION RECORD

REV	ECN	DESCRIPTION	DWTT	DATE
1		版面更新	HW	05/04/08
2		增加QC字样	WLM	01/12/09
3	06-009	增加DIP2列字及修改参数	ZXX	10/21/10



Notes:

1. Pitch: 5.08mm , Poles: XXP
2. Rated voltage/current: UL 300V/10A VDE 250V/15A $\Delta 3$
3. Operation temperatures: -40°C~+105°C
4. Withstanding Voltage: AC2000V/1Min
5. Insulation Resistance: 5000M Ω /DC1000V
6. Wire Range: 22~16AWG, 0.2~1.5mm² $\Delta 3$
7. Undimensioned Tolerances:

Pitch range in mm	Nominal dimension range in mm	—
over 6 to 10	over 10 to 24	over 30 to 60 to 100 to 150
±0.10	±0.15	±0.2±0.3 ±0.5±0.7 ±1
		0.05/10

5	DG142 Spring	X000000130 (H)	XX	Stainless Steel
4	DG142R Pin header	3005800010 (H)	XX	Brass
3	DG142-5.08 Button	300300501A (H)	XX	PA66
2	DG142-5.08 Cover	300300701A (H)	1	PA66

DETACHED LISTS

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES
1	DG142R-5.08 Housing	3005A0101A (H)	XX	PA66	UL94V-0

MM	0 ± .00 ±	±	±
ANGLES ± 1°			
THIRD ANGLE PROJECTION			

DATE	02/09/05
DATE	
DATE	
DATE	

NAME	DG142R-5.08-XXP-1Y-00A(H)
DRAWING NO.	DG142R-5.08-E04
/PART NO.	
DO NOT SCALE DRAWING	

SIZE	A3
REV	13
REV	10/21/10

8 7 6 5 4 3 2 1